


- 1.尺寸(直徑 x 高) : C1□78 x 102mm ; D1□78 x 129mm ; S1□78 x 201mm
- 2.編號內之□係接頭之種類，請依需要選擇下列代碼：
B(1/4"NPT Male) D(1/2"NPT Male) H(3/8"外徑) N(1-1/2"衛生級Female)
- 3.適用之滅菌方式編號之最後一字為S的產品，已經EOG滅菌；其他編號產品可以EOG或高壓滅菌處理
- 4.下列編號產品，於出廠時內部已清洗過：CCS 020□1 □R，045□1 □R



ADVANTEC 過濾心用過濾器 Cartridge Housings

編號	材質	適用之過濾心	In/Out	耐熱	尺寸φ XH
PSF-500P	Polysulfone	□-C10S	1/2"PTF	90°C	105x100mm
PSF-1000P	Polysulfone	□-D10S	1/2"PTF	90°C	105x130mm
PSF-2000P	Polysulfone	□-E10S	1/2"PTF	90°C	105x200mm
MTA-500T	SUS-316	□-C10S	1/2"PTF	極高	76x100mm
MTA-1000T	SUS-316	□-D10S	1/2"PTF	極高	76x130mm
MTA-2000T	SUS-316	□-E10S	1/2"PTF	極高	76x200mm
MS-500T	SUS-316	□-C10S	1-1/2"SIDF	極高	76x120mm
MS-1000T	SUS-316	□-D10S	1-1/2"SIDF	極高	76x150mm
MS-2000T	SUS-316	□-E10S	1-1/2"SIDF	極高	76x220mm

耐壓：PSF(5Kg/cm²)
MTA/MS(7Kg/cm²)



過濾心 PSF MS MTA

ADVANTEC 過濾膜濾心·過濾膜濾心用過濾器 密封式過濾膜過濾器耐化性表

溶劑名稱	過濾膜濾心·密封式過濾膜過濾器				過濾膜濾心用過濾器	
	MCS/CCS	MCF/CCF	MCP/CCP	MCG/CCG	Polysulfone	S. S.
酸類	35% Hydrochloric Acid	●	●	●	▲	●
	20% Sulfuric Acid	●	●	●	▲	●
	20% Nitric Acid	◆	▲	▲	x	●
	5% Acetic Acid	●	●	●	●	●
	20% Acetic Acid	●	●	●	▲	●
鹼類	10% Hydrofluoric Acid	◆	●	●	x	●
	5% Sodium Hydroxide	●	●	●	▲	●
	20% Sodium Chlorite	◆	●	●	●	▲
醇類	10% Ammonium Hydroxide	●	●	●	▲	●
	Methyl Alcohol	●	●	●	▲	●
	Ethyl Alcohol	●	●	●	▲	●
	Bthyl Alcohol	●	●	●	▲	●
醚類	Ethylene Glycol	●	●	●	●	●
	Ethylether	▲	▲	▲	x	x
酮類	Dioxane	▲	▲	▲	x	x
	Tetrahydrofuran	x	▲	▲	x	x
	Methyl Acetate	◆	▲	▲	▲	x
酯類	Ethyl Acetate	x	▲	▲	▲	x
	Acetone	x	●	●	x	x
酮類	Methyl Ethyl ketone(MEK)	x	▲	▲	x	x
	Methyl Isobutyl Ketone(MIBK)	x	▲	▲	x	x
	n Hexane	▲	▲	▲	▲	●
氫化合物	Cyclohexane	▲	▲	▲	▲	●
	Benzene	▲	▲	▲	▲	x
	Toluene	x	▲	▲	x	x
	Xylene	◆	▲	▲	▲	x
	Chloroform	x	▲	▲	x	x
鹵碳氫化合物	Carbon Tetrachloride	◆	▲	▲	▲	x
	Methylene Chloride	x	▲	▲	x	x
	Trichlorethane	◆	▲	▲	▲	x
	Trichlorethlene	◆	▲	▲	x	x
氨	Diethyl Acetamide	x	●	●	x	x
乙醛	Aceto Aldehyde	◆	◆	◆	◆	x
	35% Fromaldehyde	●	●	●	●	x
其它	Acetonitrile	◆	▲	▲	◆	x
	Pyridine	◆	▲	▲	x	x
	Nitrobenzene	◆	◆	◆	◆	x

● 適合使用 ▲ 特定條件下可使用 x 不適合使用 ◆ 無參考數據